



AdvantaSil High Pressure silicone tubing is a high quality, cost effective solution designed for increased flow rates to reduce your processing time. AdvantaSil High Pressure is the optimal choice for Single-Use applications such as TFF, virus filtration, inline integrity testing of filtration assemblies, and high volume fluid transfer.

AdvantaSil High Pressure tubing has undergone extensive physical, chemical and biological testing and meets USP Class VI, FDA CFR 177.2600, ISO 10993, European Pharmacopoeia 3.1.9 and other standards. Full BPOG standardized extractables test protocol has been performed by a fully-accredited, third-party test lab.



KEY FEATURES

- Allows for processing at higher flow rates
- Full vacuum capabilities on most sizes
- Flexible and translucent yet durable
- Eliminates particulate shedding that can occur when cutting braid reinforced hose
- Certified free of animal-derived ingredients
- General temperature range: -65°F (-53.9°C) to 400°F (204.4°C)
- Resists temperature extremes, compression set, chemical attack, ozone, radiation, moisture and environmental exposure
- Sterilizable by autoclave or gamma irradiation
- Available with validated sterility assurance of 10⁻⁶ via gamma irradiation per ISO 11137 method Vdmax 25
- Documented lot traceable with identification on packaging
- Documented quality control per ISO 9001:2015
- Included in our Rx-360 Joint Audit Program for Single-Use Systems



Specific cutting techniques are strongly recommended for APHP. The tubing must be cut with a chevron style cutter at a 90 degree angle to the tubing. View cutter product details at <https://www.lislecorp.com/specialty-tools/hose/hose-cutter>.

SILICONE

www.advantapure.com

Complete validation package available on request

Full BPOG standardized extractables test results available on request

SPECIFICATIONS

Product Number	Nominal I.D.		Wall		O.D.		Bend Radius		Standard Available Length (ft.)
	(in.)	(mm)	(in.)	(mm)	(in.)	(mm)	(in.)	(mm)	
APHP-0125-0250	.125	3.18	.063	1.60	.250	6.35	.375	9.5	50
APHP-0250-0375	.250	6.35	.063	1.60	.375	9.52	1	25	50
APHP-0375-0625	.375	9.52	.125	3.18	.625	15.88	1.2	30	50
APHP-0500-0750	.500	12.70	.125	3.18	.750	19.05	1.8	46	50
APHP-0750-1000	.750	19.05	.125	3.18	1.000	25.40	2.1	53	50
APHP-1000-1375	1.000	25.40	.188	4.77	1.375	34.93	4.1	104	50

Product Number	Burst Pressure Non-Treated		Recommended Working Pressure based on 3:1 safety factor Non-Treated		Burst Pressure Gamma Irradiated 45 kGy		Recommended Working Pressure based on 3:1 safety factor Gamma Irradiated, 45 kGy		Vacuum Capability (in./Hg)
	(psi)	(bar)	(psi)	(bar)	(psi)	(bar)	(psi)	(bar)	
APHP-0125-0250	244	16.8	81	5.6	289	19.9	96	6.7	>29.5
APHP-0250-0375	125	8.6	42	2.9	144	9.9	48	3.3	>29.5
APHP-0375-0625	177	12.2	59	4.1	211	14.5	70	4.8	>29.5
APHP-0500-0750	140	9.7	47	3.2	157	10.8	52	3.6	>29.5
APHP-0750-1000	109	7.5	36	2.5	123	8.5	41	2.8	>29.5
APHP-1000-1375	115	7.9	38	2.6	131	9	44	3	>29.5

Sold by standard coil length of 50 ft. Add length suffix code "L" to product number when ordering. Example: 50 ft. of .250 in. I.D. x .375 in. O.D. tubing is product number APHP-0250-0375L.

Non-listed sizes and custom lengths are available by special order.

Coils are supplied double bagged in heat-sealed polybags and bulk packed.

Contact your AdvantaPure Sales Representative regarding any special product or packaging needs.

Recommended working pressures are calculated from burst testing using a 3:1 safety factor. Testing was performed at ambient temperature. Application testing is recommended.

CF = Consult factory



Made in U.S.A.



Also available as mini and standard Tri-Clamp® ends — call for details!

APHP requires proper cutting techniques for optimal performance. See the instruction video at <http://www.advantapure.com/high-pressure-silicone-tubing.htm>.

SILICONE

Address: NewAge Industries AdvantaPure®
145 James Way
Southampton, PA 18966 U.S.A.

Toll Free Phone: **888-755-4370**
Phone: **215-526-2151**
Toll Free Fax: **888-258-4293**
Fax: **215-526-2167**
Web Site: **www.advantapure.com**
E-mail: **sales@advantapure.com**



DISTRIBUTED BY:

PHARMASEP

Always by your side

E-mail : contact@pharmasep.fr
www.pharmasep.fr - Tél : +33 4 74 71 94 71
260, rue Georges Charpak - 01390 Civrieux - France

©2021 NewAge® Industries, Inc. Specifications are subject to change without notice. AdvantaPure products are produced by NewAge® Industries, Inc. AdvantaSil®, NewAge Industries AdvantaPure®, Purity in Fluid Flow Systems®, NewAge®, and the "N" logo are registered trademarks of NewAge® Industries, Inc.

WARRANTY: NewAge Industries AdvantaPure products are warranted to be free from defects in material and workmanship. Any product found to carry such defects will be replaced without charge. This warranty is limited only to the replacement of NewAge Industries AdvantaPure products, item for item, which after examination by NewAge Industries AdvantaPure are deemed defective. NewAge Industries AdvantaPure specifically disclaims any other liability. The data supplied is provided as a helpful guideline and is believed to be reliable; however, nothing stated shall constitute a guarantee, recommendation, or warranty for any application.

NOTICE: NewAge Industries, Inc. has been a privately owned corporation since 1954. Neither the corporation nor its principals are affiliated, in any way, with any other group or entity either representing themselves as or being referred to by the term NewAge.

